

Cylindrical Roller Bearings **EW Series**

NSK has developed a higher load-carrying capacity pressed cage with low noise and superior cage strength. Our EW series is a standard cylindrical roller bearing that facilitates interchangeability across the globe, while offering better performance for every application.



Cylindrical Roller Bearing

EW Series

A newly developed standard bearing



NSK has been supplying a standard cage for smaller-sized, single row cylindrical roller bearings as indicated here:

Standard bearings——W type (Pressed steel cage with flaps)

High load-carrying E type——ET type (Polyamide resin cage)

In the 21st century, you can now take advantage of NSK's newly developed cylindrical roller bearing, the EW series, which combines the strengths and technologies of previous cages into a one-piece steel cage.

NSK has achieved a new design involving even newer concepts, while maintaining excellence in function and service life. Our EW series can meet your high load-carrying capacity needs for the new era.


Design concept of our newly developed standard bearing—the EW series

EW Series Bearing Interchange Guide


Internal design comparison of the W series and EW series

W Series (Conventional type)


EW Series (Newly developed type)



W Series




EW Series




Results of FEM analysis

EW Series




Conventional W Series




Tests confirm that the stress levels of NSK's EW series cages are 40% lower than that of cages in conventional W series.

Cage strength test results




NSK's EW series showed greater cage strength performance than that of our major competitors.

Noise measurement test results




Measuring conditions
 Bearing number: NU308
 Method: JIS B1548
 Radial load: 392 N
 Speed: 1 200 to 1 800 rpm




The EW series is 3 to 7 dB quieter than that of our major competitors.

Higher Limiting Speed








The limiting speed of the EW series is 10-25% higher than that of conventional W series.

Higher Load Rating



The load rating of the EW series is 10-60% higher than that of conventional W series.

EW Series Bearing Table



EW series 305-311 and 205-213 of NU, NJ, NUP.

d	Boundary Dimensions (mm)					Basic Load Ratings				Limiting Speeds [rpm]		Bearing Numbers			Abutment and Fillet Dimensions (mm)						Permissible Axial Movement (mm)		
	D	B	r min	r ₁ min	F _w	C _r [N]	C _{or}	C _r [kgf]	C _{or}	Grease	Oil	NU	NJ	NUP	d _a min	d _b min	d _b max	d _c min	d _d min	D _a max		r _a max	r _b max
25	52	15	1	0.6	31.5	29 300	27 700	2 990	2 830	12 000	14 000	NU205EW	NJ	NUP	30	29	30	34	37	47	1	0.6	1.2
	62	17	1.1	1.1	34	41 500	37 500	4 250	3 800	10 000	12 000	NU305EW	NJ	NUP	31.5	31.5	32	37	40	55.5	1	1	1.2
30	62	16	1	0.6	37.5	39 000	37 500	4 000	3 800	9 500	12 000	NU206EW	NJ	NUP	35	34	36	40	44	57	1	0.6	1.2
	72	19	1.1	1.1	40.5	53 000	50 000	5 400	5 100	8 500	10 000	NU306EW	NJ	NUP	36.5	36.5	39	44	48	65.5	1	1	1.2
35	72	17	1.1	0.6	44	50 500	50 000	5 150	5 100	8 500	10 000	NU207EW	NJ	NUP	41.5	39	42	46	50	65.5	1	0.6	1.2
	80	21	1.5	1.1	46.2	66 500	65 500	6 800	6 650	7 500	9 500	NU307EW	NJ	NUP	43	41.5	44	48	53	72	1.5	1	1.2
40	80	18	1.1	1.1	49.5	55 500	55 500	5 700	5 650	7 500	9 000	NU208EW	NJ	NUP	46.5	46.5	48	52	56	73.5	1	1	1.2
	90	23	1.5	1.5	52	83 000	81 500	8 500	8 300	6 700	8 000	NU308EW	NJ	NUP	48	48	50	55	60	82	1.5	1.5	1.2
45	85	19	1.1	1.1	54.5	63 000	66 500	6 450	6 800	6 700	8 000	NU209EW	NJ	NUP	51.5	51.5	52	57	61	78.5	1	1	1.2
	100	25	1.5	1.5	58.5	97 500	98 500	9 950	10 000	6 000	7 500	NU309EW	NJ	NUP	53	53	56	60	66	92	1.5	1.5	1.4
50	90	20	1.1	1.1	59.5	69 000	76 500	7 050	7 800	6 300	7 500	NU210EW	NJ	NUP	56.5	56.5	57	62	67	83.5	1	1	1.7
	110	27	2	2	65	110 000	113 000	11 200	11 500	5 000	6 000	NU310EW	NJ	NUP	59	59	63	67	73	101	2	2	1.4
55	100	21	1.5	1.1	66	86 500	98 500	8 800	10 100	5 600	7 100	NU211EW	NJ	NUP	63	61.5	64	68	73	92	1.5	1	1.2
	120	29	2	2	70.5	137 000	143 000	14 000	14 600	4 500	5 600	NU311EW	NJ	NUP	64	64	68	72	80	111	2	2	1.4
60	110	22	1.5	1.5	72	97 500	107 000	9 950	10 900	5 300	6 300	NU212EW	NJ	NUP	68	68	70	75	80	102	1.5	1.5	1.2
65	120	23	1.5	1.5	78.5	108 000	119 000	11 000	12 100	4 800	5 600	NU213EW	NJ	NUP	73	73	76	81	87	112	1.5	1.5	1.4

Worldwide Sales Offices

NSK Ltd. –Headquarters, Tokyo, Japan	www.nsk.com	Korea:		Netherlands:	
ASIA BUSINESS STRATEGIC DIVISION-HEADQUARTERS	tel: 03-3779-7145	NSK Korea Co., Ltd.	www.kr.nsk.com	NSK European Distribution Centre B.V.	
INDUSTRIAL MACHINERY BEARINGS DIVISION-HEADQUARTERS	tel: 03-3779-7227	Seoul	tel: 02-3287-0300	Tilburg	tel: 013-4647647
AUTOMOTIVE DIVISION-HEADQUARTERS	tel: 03-3779-7189	Changwon Plant	tel: 055-287-6001	Poland:	
NEEDLE ROLLER BEARINGS STRATEGIC DIVISION-HEADQUARTERS	tel: 03-3779-2563	Malaysia:		NSK Europe Ltd. Warsaw Liaison Office	
PRECISION MACHINERY & PARTS DIVISION-HEADQUARTERS	tel: 03-3779-7219	NSK Bearings (Malaysia) Sdn. Bhd.	tel: 03-7722-3373	Warsaw Liaison	tel: 022-645-1525, 1526
		Kuala Lumpur	tel: 03-8961-6288	NSK Iskra S.A.	
		NSK Micro Precision (M) Sdn. Bhd.	tel: 03-8961-6288	Kielce	tel: 041-367-0505
		Malaysia Plant		NSK European Technology Center, Poland Office	tel: 041-366-5812
		New Zealand:		NSK Steering Systems Europe (Polska) Sp.zo.o	tel: 074-664-4101
		NSK New Zealand Ltd.	www.nsk-rhp.co.nz	Spain:	
		Auckland	tel: 09-276-4992	NSK Spain S.A.	
Africa		Philippines:		Barcelona	tel: 093-289-27-63
South Africa:		NSK Representative Office		Turkey:	
NSK South Africa (Pty) Ltd.	tel: 011-458-3600	Manila	tel: 02-759-6246	NSK Bearings Middle East Trading Co., Ltd.	
Johannesburg		Singapore:		Istanbul	tel: 0216-442-7106
Asia and Oceania		NSK International (Singapore) Pte Ltd.		United Kingdom:	
Australia:		Singapore	tel: 65-6278-1711	NSK Bearings Europe Ltd.	
NSK Australia Pty. Ltd.	www.nskaustralia.com.au	NSK Singapore (Pte) Ltd.	www.nsk-singapore.com.sg	Peterlee Plant	tel: 0191-586-6111
Melbourne	tel: 03-9764-8302	Singapore	tel: 65-6278-1711	NSK European Technology Centre	tel: 01636-605123
China:		Taiwan:		Newark	tel: 01636-605123
NSK Hong Kong Ltd.	tel: 2739-9933	Taiwan NSK Precision Co., Ltd.	tel: 02-2509-3305	NSK UK Ltd.	tel: 01636-605123
Hong Kong		Taipei		NSK Precision UK Ltd.	tel: 01636-605123
Kunshan NSK Co., Ltd.	tel: 0512-5771-5654	Thailand:		Newark	tel: 01636-605123
Kunshan Plant	tel: 0512-5283-2938	NSK Bearings (Thailand) Co., Ltd.	tel: 02-6412-150	NSK Steering Systems Europe Ltd.	tel: 024-76-588588
Changshu NSK Needle Bearing Co., Ltd.	tel: 0512-5283-2938	Bangkok	tel: 038-454010-454016	Coventry	
Jiangsu Plant	tel: 0512-5283-2938	NSK Bearings Manufacturing (Thailand) Co., Ltd.	tel: 038-522-343-350	North and South America	
Guizhou HS NSK Bearings Co., Ltd.	tel: 0853-3521505	Chonburi	tel: 038-454631-454633	NSK Americas, Inc. (American Headquarters)	
Anshun Plant	tel: 0769-262-0960	SIAM NSK Steering Systems Co., Ltd.	tel: 038-522-343-350	Ann Arbor	tel: 734-913-7500
NSK Steering Systems Dongguan Co., Ltd.	tel: 0769-262-0960	Chachoengsao	tel: 038-522-343-350	Argentina:	
Dongguan Plant	tel: 0512-5867-6496	NSK Asia Pacific Technology Center (Thailand) Co., Ltd.	tel: 038-454631-454633	NSK Argentina SRL	
Zhangjiagang NSK Precision Machinery Co., Ltd.	tel: 0512-6665-5666	Chonburi		Buenos Aires	tel: 11-4704-5100
Jiangsu Plant	tel: 0512-6665-5666	Vietnam:		Brazil:	
Timken-NSK Bearings (Suzhou) Co., Ltd.	tel: 0512-6665-5666	NSK Representative Office		NSK Brasil Ltda.	www.br.nsk.com
Jiangsu Plant	tel: 0512-6665-5666	Hanoi	tel: 04-935-1269	São Paulo	tel: 011-3269-4723
NSK China Technology Center	tel: 0512-6665-5666	Europe		Canada:	
Jiangsu	tel: 0512-6665-5666	NSK Europe Ltd. (European Headquarters)		NSK Canada Inc.	www.ca.nsk.com
NSK (Shanghai) Trading Co., Ltd.	tel: 021-6235-0198	Maidenhead, U.K.	www.eu.nsk.com	Toronto	tel: 905-890-0740
Shanghai	tel: 021-6235-0198	France:		Mexico:	
NSK Representative Offices	www.nsk.com.cn	NSK France S.A.S	tel: 01-30-57-39-39	NSK Rodamientos Mexicana, S.A. de C.V.	www.mx.nsk.com
Beijing	tel: 010-6590-8161	Paris		Mexico City	tel: 55-5390-4312
Guangzhou	tel: 020-3786-4833	Germany:		United States of America:	
Anshun	tel: 0853-3522522	NSK Deutschland GmbH	tel: 02102-481-0	NSK Corporation	www.us.nsk.com
Chengdu	tel: 028-8661-4200	Düsseldorf	tel: 02102-481-0	Ann Arbor	tel: 734-913-7500
Shenzhen	tel: 0755-25904886	Düsseldorf	tel: 02102-481-0	NSK American Technology Center	tel: 734-913-7500
Changchun	tel: 0431-8988682	Stuttgart	tel: 0771-79082-277	Ann Arbor	tel: 734-913-7500
NSK (China) Investment Co., Ltd.	tel: 021-6235-0198	Neuweg Fertigung GmbH	tel: 0771-79082-277	NSK Precision America, Inc.	www.npa.nsk.com
Shanghai	tel: 021-6235-0198	Munderkingen	tel: 07393-540	Franklin	tel: 317-738-5038
India:		Italy:		NSK Steering Systems America, Inc.	www.nssa.nsk.com
Rane NSK Steering Systems Ltd.	tel: 044-274-66002	NSK Italia S.p.A.	tel: 02-995-19-1	Bennington, Vermont	tel: 802-442-5448
Chennai	tel: 044-2446-6862	Milano	tel: 02-995-19-1	NSK Latin America, Inc.	www.la.nsk.com
NSK Ltd. India Blanch Office	tel: 044-2446-6862	Industria Cuscinetti S.p.A.	tel: 0119824811	Miami	tel: 305-477-0605
Chennai	tel: 044-2446-6862	Torino Plant	tel: 0119824811		
Indonesia:					
PT. NSK Bearings Manufacturing Indonesia	tel: 021-898-0155				
Jakarta	tel: 021-898-0155				
PT. NSK Indonesia	tel: 021-252-3458				
Jakarta	tel: 021-252-3458				

NSK Ltd. has a basic policy not to export any products or technology designated as controlled items by export-related laws. When exporting the products in this brochure, the laws of the exporting country must be observed. Specifications are subject to change without notice and without any obligation on the part of the manufacturer. Every care has been taken to ensure the accuracy of the data contained in this brochure, but no liability can be accepted for any loss or damage suffered through errors or omissions. We will gratefully acknowledge any additions or corrections.

For more information about NSK products, please contact: _____



Printed on 100% recycled paper.